




CGA Standards




Connection 110 5/16" – 32 RH INT., with Gasket




Connection 160 1/8" – 27 NGT RH INT.




Connection 165 0.4375" – 20 UNF 2A RH EXT.




Connection 170 9/16" – 18 RH EXT. and 5/16" – 32 RH INT., with Gasket




Connection 180 0.625" – 18 UNF 2A RH EXT., with Gasket




Connection 240 3/8" – 18 NGT – RH INT.




Connection 296 0.803" – 14 RH INT.




Connection 300 0.825" – 14 NGO RH EXT.




Connection 320 0.825" – 14 RH EXT., with Gasket




Connection 326 0.825" – 14 RH EXT.




Connection 330 0.825" – 14 LH EXT., with Gasket




Connection 346 0.825" – 14 NGO RH EXT.



Connection 350 0.825" – 14 LH EXT.




Connection 410 0.85" – 14NGO LH EXT.




Connection 510 0.885" – 14 LH INT.


CGA Standards continued




Connection 540 0.903" – 14 RH EXT.




Connection 555 0.903" – 14NGO LH EXT.




Connection 580 0.965" – 14 RH INT.




Connection 590 0.965" – 14NGO LH INT.




Connection 600 1" – 20 UNEF RH EXT.,
with Gasket




Connection 630 1.03" – 14NGO RH EXT.




Connection 632 1.03" – 14NGO RH EXT.




Connection 634 1.03" – 14NGO RH EXT.




Connection 636 1.03" – 14NGO RH EXT.




Connection 638 1.03" – 14NGO RH EXT.




Connection 640 1.03" – 14NGO RH EXT.




Connection 642 1.03" – 14NGO RH EXT.



Connection 660 1.03" – 14 RH EXT.,
with Gasket




Connection 677 1.03" – 14NGO LH EXT.




Connection 705 1.125" – 14 UNS 2A RH
EXT., with Gasket


CGA Standards continued




Connection 710 1.125" – 14NGO RH EXT.




Connection 712 1.125" – 14NGO RH EXT.




Connection 714 1.125" – 14NGO RH EXT.




Connection 716 1.125" – 14NGO RH EXT.




Connection 718 1.125" – 14NGO RH EXT.




Connection 720 1.125" – 14NGO RH EXT.




Connection 722 1.125" – 14NGO RH EXT.




Connection 724 1.125" – 14NGO RH EXT.




Connection 726 1.125" – 14NGO RH EXT.




Connection 728 1.125" – 14NGO RH EXT.




Connection 024 0.875" – 14UNF RH EXT.



Connection 025 0.875" – 14UNF LH EXT.



Connection 034 0.875" – 14UNF RH EXT.



Connection 035 0.875" – 14UNF LH EXT.